


XP-329ⅢR



Your Authorized New Cosmos Distributor:

Minerva Industrial & Trading Pte Ltd
 T: 6848 5155
 E: sales@minerva-intra.com
 W: www.minerva-intra.com.sg

Features

- Instant digital display of odor intensity.

Applications

- Performance check on deodorizing apparatus and air cleaners.
- Measuring smells of factory exhaust, waste water, and drainage.
- Quality control of foods and spices.

Specifications

Model	XP-329ⅢR
Substance Measured	Various odors, odor components
Detection Principle	Indium oxide-based sensitivity hot wire semiconductor sensor
Sampling Method	Extractive *Extractive flow: 400±150ml/min
Display	LCD digital indication (64 × 128 dots matrix) (measurement value, measurement mode, operating conditions, remaining battery level, data memory, bar indication for sensor output and communication channel etc.)
Measurement Mode	Monitoring mode • Batch mode
Detection Range	Level indication: 0-2000 (In case of zero-based setting at the 2nd dot from the left in the sensor output bar graph)
Repeatability	Measurement value ±5% ±1 digit *1 level indication
Response Time	20s or less (90% response) by calibrated odor
External Output	Analog output: Level indication: 0000-2000 corresponding to DC0-200 mV. (0.1mV as contrasted with indication 1) (Except approx. 204.8mV in case of OVER LEVEL) Digital input/output: RS-232C output the indicated value (ASCII Code) (Except in case of OVER LEVEL, output [****])
External Output Terminal	DIN connector for both analog output and digital input/output
Operating Temperature and Humidity	Temperature: 0 to 40°C Humidity: 10-80%RH (non-condensing)
Dimensions	W84 × H275 × D40mm (excluding protrusions)
Weight	Approx. 640g (including batteries)
Power Source	4 × AA alkaline dry cells or AC adaptor
Battery Life	Up to 8 hours by alkaline cells, low battery alarm function
Standard Accessories	Activated carbon filter, Drain filter, Sample draw attachment, Tube intake, AC adaptor, Carrying case, Output connector, Communication pack (CD), 4 × AA alkaline dry cells, Teflon tube (1m), 2 × Activated carbons, 2 × Filter elements (10 pcs.), Instruction manual, Test report

*1 Under identical measuring conditions.